# **DIO Indoor Transitions TVX**



### **Specification**

Material	TVX
Refractive Index	1.53
Gravity	1.11
Abbe Value	45
UV cut off (mm)	400
Color	Grey/Brown

Addition (dpt)	0.75~3.50
Base curve	2.25~8.25BC
Max Diameters (mm)	76
Fitting Height (mm)	14/16/18
Available Corridor length (mm	9/11/13
ID Mark	INF

#### **Lens Features**

Specially tailored indoor progressive lens

Distortion free room distance clear vision from 0.4mm to2


Wider intermediate & near vision

For all indoor activities (Meeting, computing, painting, reac


Order just as normal progressive lenses

(DIO design software will convert power to be produced)

#### **Power Chart**



## **Lens Marking Layout**



#### **Add-on Features**

Precal

Remote Edging

Special thickness

Rx compensation

Decentration

Hi cylinder (4-6)

Prism ( $\leq 4 \Delta$ )

Mirror coating

\* When your prescription is over of range, please contact us directly.

65R

Addition = +2.00

Index = Lens Index

70R